# Success Story 03/2019


3D milling - ISO 00P with BCH30M



# Application

Country Austria Material 1.4543 Coolant dry

### Solution



### **Boehlerit:**

BF00 RD10.042 Z05 RDKW 1003MOS-RH BCH30M

completely different cutting system, tool life was increased from 16 pieces up to 404 pieces

Customer's benefit

Through the usage of a

## **Competitor:**

Cutter Ø 40 mm with 6 teeth SDMT090308 VU10

#### Cutting data:

 $v_c = 70 / 90 \text{ m/min}$   $f_z = 0.36 / 0.32 \text{ mm}$  $a_p = 0.4 / 0.2 \text{ mm}$ 

#### Result:

8 - 16 pieces

# Cutting data:

 $v_c = 70 / 90 \text{ m/min}$   $f_z = 0.44 / 0.38 \text{ mm}$  $a_p = 0.4 / 0.2 \text{ mm}$ 

#### Result:

404 pieces

#### **Tool life**

